

PANDUIT Wiring Accessories



RoHS Compliant This product is RoHS compliant.

WIRING ACCESSORIES

For quantities of 5000 and up, call for quote.

Cable Tie Mounts

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-ABM2S-A-D	A	ABS	Rubber	4-way Adh Backed	White	1.0 x 1.0	.75	.61	.55	.42
644-ABM2S-AT-D	A	ABS	Acrylic	4-way Adh Backed	White	1.0 x 1.0	.66	.57	.54	.49
644-ABM3H-A-L	A	Nylon 6.6	Rubber	4-way Adh Backed	White	1.5 x 1.5	2.01	1.78	1.56	1.30
644-ABM1M-A-M	A	Nylon 6.6	Rubber	4-way Adh Backed	White	.50 x .50	.90	.73	.66	.48
644-ABM1M-AT-M	A	Nylon 6.6	Acrylic	4-way Adh Backed	White	.50 x .50	1.17	.55	.49	.43
644-ABM100-A-D	A	Nylon 6.6	Rubber	4-way Adh Backed	White	1.0 x 1.0	1.29	1.17	1.06	.88
644-ABM100-AT-D	A	Nylon 6.6	Acrylic	4-way Adh Backed	White	1.0 x 1.0	.67	.60	.55	.50
644-ABMM-A-D	A	ABS	Rubber	4-way Adh Backed	White	.75 x .75	.95	.86	.78	.67
644-ABMM-AT-D	A	ABS	Acrylic	4-way Adh Backed	White	.75 x .75	.52	.46	.44	.39
644-ABM4H-A-T	A	Nylon 6.6	Rubber	4-way Adh Backed	White	2.0 x 2.0	1.46	1.29	1.23	1.10
644-ABMS-A-D	B	Nylon 6.6	Rubber	2-way Adh Backed	Natural	1.13 x 1.13	.76	.69	.61	.48
644-ABMT-A-C	C	Nylon 6.6	Rubber	Rubber	Natural	1.10 x 1.12	1.94	1.67	1.53	1.41
644-PWMS-H2S-C	D	Nylon 6.6	---	Push Barb	Natural	.37 x .75	.41	.34	.31	.26
644-TM1S4-M	E	Nylon 6.6	---	#4 (M2.5) Screw	Natural	.32 x .51	.20	.19	.18	.16
644-TM2S6-M	E	Nylon 6.6	---	#6 (M3) Screw	Natural	.43 x .63	.18	.17	.14	.13
644-TM2S8-M	E	Nylon 6.6	---	#8 (M4) Screw	Natural	.43 x .63	.18	.17	.14	.13
644-TM3S10-M	E	Nylon 6.6	---	#10 (M5) Screw	Natural	.62 x .86	.33	.29	.28	.25
644-TM3S8-M	E	Nylon 6.6	---	#8 (M4) Screw	Natural	.62 x .86	.73	.57	.51	.25
644-TM3S25-M	E	Nylon 6.6	---	1/4 (M6) Screw	Natural	.62 x .86	.32	.29	.27	.25
644-TM3R6-M	E	Nylon 6.6	---	#6 (M3) Rivet	Natural	.62 x .86	.32	.29	.27	.25

Wire Mounting Devices

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-ARC.68-A-C	F	Polypro.	Rubber	Rubber Adhesive	Natural	1.0 x 1.0	.76	.68	.58	.52
644-ARC.68-A-C14	F	Polypro.	Rubber	Rubber Adhesive	Gray	1.0 x 1.0	.91	.83	.76	.64
644-ARC.68-S6-C	F	Polypro.	---	#6 (M3) Screw	Natural	1.0 x 1.0	.50	.45	.43	.38
644-ARC.68-S6-C14	F	Polypro.	---	#6 (M3) Screw	Gray	1.0 x 1.0	.57	.46	.39	.38
644-ACC19-A-M	G	Nylon 6.6	Rubber	Adhesive Backed	Natural	.62 x .75	.70	.63	.56	.48
644-ACC38-A-M	G	Nylon 6.6	Rubber	Adhesive Backed	Natural	1.0 x 1.0	.82	.75	.67	.55
644-AJC12-A-C	H	PVC	Rubber	Rubber	Lt. Gray	.86 x 1.0	.44	.39	.31	.25
644-AJC25-A-C	H	PVC	Rubber	Rubber	Lt. Gray	.97 x 1.5	.42	.38	.32	.25
644-CCH12-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x 0.125	.24	.08	.07	.06
644-CCH19-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x 0.187	.24	.08	.07	.06
644-CCH25-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x 0.25	.20	.18	.15	.14
644-CCH31-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x 0.312	.26	.10	.08	.07
644-CCH38-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x 0.375	.26	.11	.10	.08
644-CCH44-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x 0.437	.26	.11	.10	.08
644-CCH50-S10-M	I	Nylon 6.6	---	#10 (M5) Screw	Natural	.50 x 0.500	.26	.11	.10	.08
644-CCS19-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x 0.187	.21	.08	.07	.06
644-CCS25-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x 0.25	.17	.15	.12	.08
644-CCS31-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x 0.312	.21	.08	.07	.06
644-CCS38-S8-C	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x 0.375	.14	.13	.10	.08
644-CCS44-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x 0.437	.23	.08	.07	.06
644-CCS50-S8-M	I	Nylon 6.6	---	#8 (M4) Screw	Natural	.37 x 0.500	.18	.17	.13	.10
644-FCC-A-C8	J	PVC	Rubber	Rubber Adhesive	Gray	1.09 x 1.00	.45	.41	.33	.27
644-WS25-50-C	K	Nylon 6.6	---	Push Barb	Natural	.50 H x 0.25	.35	.31	.27	.23
644-WS50-25-C	K	Nylon 6.6	---	Push Barb	Natural	.25 H x 0.50	.39	.34	.28	.24
644-WS50-50-C	K	Nylon 6.6	---	Push Barb	Natural	.50 H x 0.50	.42	.36	.29	.25
644-CBP12-C	L	Nylon 6.6	---	Push Barb	Natural	.125 standoff H	.23	.21	.16	.13
644-CBP25-C	L	Nylon 6.6	---	Push Barb	Natural	.250 standoff H	.23	.21	.16	.14
644-CBP37-C	L	Nylon 6.6	---	Push Barb	Natural	.375 standoff H	.23	.21	.16	.14
644-CBP50-C	L	Nylon 6.6	---	Push Barb	Natural	.500 standoff H	.23	.21	.17	.15
644-CBLS25-C	M	Nylon 6.6	---	Push Barb	Natural	.250 standoff H	.22	.20	.14	.13
644-CBLS50-C	M	Nylon 6.6	---	Push Barb	Natural	.500 standoff H	.24	.22	.18	.14
644-CBLS75-C	M	Nylon 6.6	---	Push Barb	Natural	.750 standoff H	.27	.21	.18	.16

Flat Cable Mounting Device

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-FCM1-A-C14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.05 x 2.90	1.26	.98	.835	.774
644-FCM1.2-A-C14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.37 x 3.16	1.56	1.22	.92	.88
644-FCM2-A-C14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	2.22 x 5.06	1.39	1.08	.99	.87
644-FCM3.25-A-L14	N	Nylon 6.6	Rubber	Rubber Adhesive	Gray	3.38 x 7.30	2.55	1.66	1.32	1.23
644-FCM1-S6-C14	N	Nylon 6.6	---	#6 (M3) Screw	Gray	1.00 x 2.90	1.20	.94	.874	.794
644-FCM1.2-S6-C14	N	Nylon 6.6	---	#6 (M3) Screw	Gray	1.37 x 3.16	1.49	1.17	.95	.89
644-FCM2-S6-C14	N	Nylon 6.6	---	#6 (M3) Screw	Gray	2.22 x 5.06	1.55	1.21	.992	.911

Latching Clip

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-LC3-A-C8	O	PVC	Rubber	Adhesive Backed	Lt. Gray	.75 x .75	.64	.56	.53	.49
644-LC5-A-C8	O	PVC	Rubber	Adhesive Backed	Lt. Gray	1.01 x 1.01	.61	.54	.51	.47
644-LC10-A-L8	O	PVC	Rubber	Adhesive Backed	Lt. Gray	1.51 x 1.51	.72	.64	.62	.56

LWC Type

For quantities of 5000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Material	Adhesive Type	Mounting Method	Color	Dimensions W x L (in.)	Price Each			
							1	100	500	1000
644-LWC19-A-M14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	.61 x .85	.33	.29	.28	.26
644-LWC25-A-C14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.00 x .88	.67	.53	.42	.38
644-LWC38-A-C14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.0 x 1.0	.73	.58	.422	.422
644-LWC50-A-L14	P	Nylon 6.6	Rubber	Rubber Adhesive	Gray	1.0 x 1.26	1.22	.96	.74	.70

DIMENSIONS: in. (mm)

A: Cable tie mount top view.

B: Cable tie mount side view.

C: Cable tie mount front view.

D: Cable tie mount detail with dimensions: .22 (5.6), .23 (5.8), .63 (16.0).

E: Wire mounting device with dimensions: Length, Width.

F: Wire mounting device side view.

G: Wire mounting device top view.

H: Wire mounting device side view.

I: Wire mounting device top view.

J: Wire mounting device side view.

K: Flat cable mounting device with dimensions: Max. Dia. (when closed), To fit .187" (4.7)/.192" (4.9) dia. hole in .03" to .08" thick panel, Standoff Height.

L: Flat cable mounting device with dimensions: .170 (4.3), .140 (3.6), .187 Dia. (4.7), A, B, .140 (3.6).

M: Latching clip with dimensions: .40 (10.2), .22 (5.6), .56 (14.2), A, B.

N: Latching clip side view.

O: LWC type side view.

P: LWC type top view.